

Stamped Bonding Plate

Power Utilities



FEATURES

Stamped bonding plate suitable for structural steel applications

Listed to UL® 96

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)


Table 1/1

Catalog Number	Contact Area	Height (H)	Width (W)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Unit Weight
LPA540	51.600 cm ² Min	31.75 mm	107.950 mm	5.1 mm	7.9 mm	0.088 kg
LPC540	51.600 cm ² Min	31.75 mm	107.950 mm	5.1 mm	7.9 mm	0.254 kg

ADDITIONAL PRODUCT DETAILS

Stainless steel separator included with LPC540A for bi-metallic applications.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE