

Low-Profile Splice Kit



nVent RAYCHEM S-150 is a cold-applied low profile splice for trace heating cables in both non-hazardous and hazardous locations. Includes cold-applied heating cable core sealer.

FEATURES

Simple and fast to install and test

Cold-applied: no heat gun or hot work permit required, re-enterable

High performance: resistant to impact, high temperature, chemicals and UV

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Table 1/2									
Catalog Number	Item Name	Model	Connection Type	Voltage Rating for FM, CSA	Voltage Rating for PTB	Current Rating for FM, CSA			
497537-000	S-150	Heating Cable/Heating Cable	Cold Applied	277 V	254 V	50 A			

Table 2/2								
Catalog Number	Item Name	Current Rating for PTB	Max Exposure Temperature	Below Insulation				
497537-000	S-150	40 A	215 °C	Yes				

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com