


RatiopacPRO/-Air Tip-up Handle, 63 HP

CATALOG NUMBER

24571-321

Tip-up carrying handles.



CERTIFICATIONS



FEATURES

Adjustable in 30° increments

Retrofittable without mechanical tooling on case

Static load-carrying capacity 30 kg

The handle enable a user to have a better view to the front side of the case in case of desktop usage

PRODUCT ATTRIBUTES

Rack Width: 63HP

Package Quantity: 1

Handle Type: Tip-up Handle

Color: Silver

Finish: Powder Coated

Material: Aluminum; ABS

Product Family: RatiopacPRO; RatiopacPRO AIR

Product Type: Handle

ADDITIONAL PRODUCT DETAILS

Cannot be used in conjunction with front handles.

Assembly kit is required for tip-up carrying handle, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE