

Leak Detection for Varistar LHX+ 45 / RackChiller In-Row 45

CATALOG NUMBER

24630-168



This leak detection package extends the Varistar LHX+ 45 In-Rack and the RackChiller In-Row 45 with the capability to detect leaks within the device. The rope sensor is installed at the rim of the condensate tray to minimize false alarms through condensate water or similar.

FEATURES

Leak detection equipment for LHX+ 45 In-Rack or RackChiller In-Row 45

Rope sensor to be installed at device's bottom panel

Includes leak detection module and accessories

PRODUCT ATTRIBUTES

Product Type: Sensor

Net Weight: 2kg

Package Quantity: 1

Product Family: RackChiller

ADDITIONAL PRODUCT DETAILS

Works only with Varistar LHX+ 45 In-Rack and RackChiller In-Row 45

This package needs to be installed into the cooler prior to commissioning of the device. It can not be retrofitted once the cooler is surrounded with racks

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE