


Novastar Rear Panel With Cable Ducting, RAL 7021, 38 U 553W

CATALOG NUMBER

25230-452



Novastar Rear Panel with 3 U or 4 U cable ducting for improved cable management.

CERTIFICATIONS



FEATURES

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

PRODUCT ATTRIBUTES

Rack Height: 38U

Height: 1711mm

Width: 553mm

Color: Black Grey

Color Code: RAL 7021

Material: Steel

Package Quantity: 1

Finish: Powder Coated

Product Family: Novastar

Product Type: Cabinet/Rack Panel

Type: Rear Panel

Net Weight: 10.602kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE