


Novastar 19" Shelf, Stationary, 1 U 600W 500D

CATALOG NUMBER

27230-051



Novastar 19" Shelf, Stationary with 75 Kg load capacity, perforated for ease of assembly.

CERTIFICATIONS



FEATURES

Mounting height 1 U, for fitting on the vertical cabinet uprights

Static load-carrying capacity 75 kg

Perforated for assembling cable ties

St, 1.5 mm

With perforation

Color RAL 7021

PRODUCT ATTRIBUTES

Width: 553mm
Depth: 500mm
Package Quantity: 1
Color: Black Grey
Color Code: RAL 7021
Finish: Powder Coated
Height: 44.45mm
Material: Steel
Product Family: Novastar
Product Type: Shelf
Type: Stationary Shelf
Net Weight: 3.82kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE