nVent | SCHROFF

We connect and protect

# 19" Distribution Panel, Cat 6

## CATALOG NUMBER

**60118-435**



19'' distribution panel for 24 Cat6 patch cable.

## CERTIFICATIONS

RoHS COMPLIANT

## FEATURES

- Meets the specifications for EN 50 173 (as at 07/95)
- Case can be opened and closed without tools through quick-release fastener
- 1 U distribution panel with 24 x RJ45 ports
- For use in communications networks, conforms to ISO/IEC 11801 (as at 03/95)
- Easy to fit thanks to dual insulation displacement technique (LSA+/110)

## PRODUCT ATTRIBUTES

- Product Type: Patch Panel
- Type: Patch Panel, Cat 6
- Works With: Cabinet
- Finish: Powder Coated
- Material: Steel
- Net Weight: 2.3kg

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.


**North America**
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

**Europe**
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

**Asia**
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

**Middle East & India**
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff


Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**


©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.