

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Non-shielded subrack for backplane mounting.



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFICATIONS

Finish: Anodized; Passivated

EMC Shielding: No

Product Type: Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Handle Included
24563-131	3U	175mm	1	Backplane	160mm	No
24563-132	3U	235mm	1	Backplane	160mm, 220mm	No
24563-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	No
24563-134	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-135	3U	415mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-136	3U	475mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-431	6U	175mm	1	Backplane	160mm	No
24563-432	6U	235mm	1	Backplane	160mm, 220mm	No
24563-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	No
24563-434	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-435	6U	415mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-436	6U	475mm	1	Backplane	160mm, 220mm, 280mm, 340mm	No

Table 2/2

Catalog Number	Mounting	Complies With	Material	Rack Width	Static Load	Quick Ship
----------------	----------	---------------	----------	------------	-------------	------------

24563-131	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-132	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-133	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-134	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-135	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-136	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-431	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-432	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-433	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-434	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-435	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No
24563-436	Rack	IEC 60297-3-103	Aluminum	84HP	11kg	No

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE