

nVent CADDY Cat HP J-Hook Clip to BC200 Beam Clamp



CERTIFICATIONS





FEATURES

Easy installation to beam flanges

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability


Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

SPECIFICATIONS

Table 1/1					
Catalog Number	Article Number	Material	Finish	Flange Thickness (FT)	Static Load
CATHPBC200	181079	Steel, Spring Steel	Electrogalvanized, nVent CADDY Armour	3.2 - 16 mm	440N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO S

SCHROFF

TRACHTE

