We connect and protect

Theft-Deterrent Grounding Busbar, Post Mount Assembly

Data Solutions

CATALOG NUMBER

TDSGAPC14

CERTIFICATIONS

FEATURES

- Mounts to a Schedule 40 pipe or post without cutting or drilling the pipe
- Accepts standard telecommunication grounding lugs (lugs not included)
- Includes 14 Standard Spacers (TDSGAS)

PRODUCT ATTRIBUTES

- Material: Copper; Stainless Steel 304 (EN 1.4301); Stainless Steel 18-8 (EN 1.4305); Nylon
- Finish: Tinned
- Spacer Thickness: 6.4mm
- Length (L): 266mm
- A: 25.4mm

Fence Post Size, Nominal: 1.5 – 2in
Fence Post Outside Diameter, Actual (Ø): 48 – 63.5mm
Thread Size 1 (TS1): 3/8" UNC
Thread Size 2 (TS2): 5/16" UNC
Thread Size 3 (TS3): 5/16" UNC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.