

TTA-SIM-1A Alarm Module

nVent RAYCHEM TraceTek TTA-SIM-1A is a primary sensor interface module with capacity to monitor up to 150 m / 500 ft of sensor cable. It can be used as a stand-alone leak detection alarm unit, or in networks with other nVent RAYCHEM TraceTek TTSIM, TT-NRM or TTDM-128 modules. Output is via relay contacts and serial data.

FEATURES

Easy set up, rugged polycarbonate enclosure

Simple operation: LEDs to indicate power, leak, cable trouble, and communication status; 60 dB audible alarm with silence button; volt-free contacts for alarm signaling; relay software selectable for normally energized or normally de-energized operation

Flexible interface options: simple twisted pair serial RS-485 communications up to 1200 m / 4000 ft with automatic protocol selection (MODBUS, Opto 22 and Metasys)

SPECIFICATIONS

NEMA Rating:	1 Indoor, electrical protection
Depth:	100 mm
Height:	120 mm
Max Length of Sensing Cable metric:	150 m
Width:	240 mm
Operating Temperature:	0 – 50 °C
IP Rating:	IP20
Relay Contacts:	SPDT, Form C

Table 1/1

Catalog Number	Item Name	Supply Voltage
P000000154	TTA-SIM-1A-230	216 – 253 V
P000000153	TTA-SIM-1A-120	96 – 132 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT