

# 19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

## CERTIFICATIONS



## FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

## SPECIFICATIONS

|                      |              |
|----------------------|--------------|
| <b>Material:</b>     | Steel; ABS   |
| <b>Product Type:</b> | Assembly Kit |
| <b>Type:</b>         | Mounting Kit |
| <b>Finish:</b>       | Zinc Plated  |

Table 1/1

| Catalog Number | Package Quantity | Thread Size | Product Family | Works With | Quick Ship |
|----------------|------------------|-------------|----------------|------------|------------|
|----------------|------------------|-------------|----------------|------------|------------|

|           |     |    |                                                                                                                                                   |                                                                                 |    |
|-----------|-----|----|---------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------|----|
| 21100-435 | 8   | M6 | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack, Outdoor | 19" Cases, 19"<br>Wallmount, 19"<br>Indoor Cabinets,<br>19" Outdoor<br>Cabinets | No |
| 21101-809 | 50  | M6 | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack, Outdoor | 19" Cases, 19"<br>Wallmount, 19"<br>Indoor Cabinets,<br>19" Outdoor<br>Cabinets | No |
| 21101-810 | 100 | M6 | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack, Outdoor | 19" Cases, 19"<br>Wallmount, 19"<br>Indoor Cabinets,<br>19" Outdoor<br>Cabinets | No |
| 21190-435 | 32  | M6 | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack, Outdoor              | 19" Cases, 19"<br>Wallmount, 19"<br>Indoor Cabinets,<br>19" Outdoor<br>Cabinets | No |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**