

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Product Family:	MultipacPRO
EMC Shielding:	No (Retrofittable)
Type:	Perforated

Table 1/1

Catalog Number	Rack Height	Depth	Usable Width	Mounting	Complies With	Quick Ship
20860-621	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No
20860-622	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No
20860-625	2U	280mm	403mm	Rack	IEC 60297-3-100	No
20860-626	2U	340mm	403mm	Rack	IEC 60297-3-100	No
20860-627	3U	280mm	403mm	Rack	IEC 60297-3-100	No
20860-628	3U	340mm	403mm	Rack	IEC 60297-3-100	No
20860-629	3U	400mm	403mm	Rack	IEC 60297-3-100	No
20860-632	4U	340mm	403mm	Rack	IEC 60297-3-100	No
20860-633	4U	400mm	403mm	Rack	IEC 60297-3-100	No
20860-634	4U	460mm	403mm	Rack	IEC 60297-3-100	No
20860-635	5U	460mm	403mm	Rack	IEC 60297-3-100	No

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE