

# RatiopacPRO Desktop Case, Retrofittable Shielding



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides a sleek design for desktop applications.

## CERTIFICATIONS



## FEATURES

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Retrofittable EMC shielding

Version with cover strips

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

No visible screws; cladding parts removable without tools

Conforms with DIN EN 62368-1

## SPECIFICATIONS

|                        |                                           |
|------------------------|-------------------------------------------|
| <b>Product Type:</b>   | Case                                      |
| <b>Type:</b>           | Case for Individual Electronic Components |
| <b>EMC Shielding:</b>  | No (Retrofittable)                        |
| <b>Product Family:</b> | RatiopacPRO                               |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|----------------|-------------|------------|---------|------------------|---------------|--------------|
| 24572-524      | 2U          | 63HP       | 375.5mm | 1                | 67.9mm        | 326mm        |
| 24572-530      | 2U          | 84HP       | 255.5mm | 1                | 67.9mm        | 432mm        |
| 24572-533      | 2U          | 84HP       | 315.5mm | 1                | 67.9mm        | 432mm        |
| 24572-534      | 2U          | 84HP       | 375.5mm | 1                | 67.9mm        | 432mm        |
| 24572-535      | 2U          | 84HP       | 435.5mm | 1                | 67.9mm        | 432mm        |
| 24572-536      | 2U          | 84HP       | 495.5mm | 1                | 67.9mm        | 432mm        |
| 24571-002      | 3U          | 28HP       | 255.5mm | 1                | 112.3mm       | 148mm        |
| 24571-005      | 3U          | 28HP       | 315.5mm | 1                | 112.3mm       | 148mm        |
| 24571-014      | 3U          | 42HP       | 255.5mm | 1                | 112.3mm       | 219mm        |
| 24571-017      | 3U          | 42HP       | 315.5mm | 1                | 112.3mm       | 219mm        |
| 24571-018      | 3U          | 42HP       | 375.5mm | 1                | 112.3mm       | 219mm        |
| 24571-026      | 3U          | 63HP       | 255.5mm | 1                | 112.3mm       | 326mm        |
| 24571-029      | 3U          | 63HP       | 315.5mm | 1                | 112.3mm       | 326mm        |
| 24571-030      | 3U          | 63HP       | 375.5mm | 1                | 112.3mm       | 326mm        |
| 24571-038      | 3U          | 84HP       | 255.5mm | 1                | 112.3mm       | 432mm        |
| 24571-041      | 3U          | 84HP       | 315.5mm | 1                | 112.3mm       | 432mm        |
| 24571-042      | 3U          | 84HP       | 375.5mm | 1                | 112.3mm       | 432mm        |
| 24571-043      | 3U          | 84HP       | 435.5mm | 1                | 112.3mm       | 432mm        |

| CatalogNumber | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|---------------|-------------|------------|---------|------------------|---------------|--------------|
| 24571-044     | 3U          | 84HP       | 495.5mm | 1                | 112.3mm       | 432mm        |
| 24571-050     | 4U          | 28HP       | 255.5mm | 1                | 156.8mm       | 148mm        |
| 24571-053     | 4U          | 28HP       | 315.5mm | 1                | 156.8mm       | 148mm        |
| 24571-062     | 4U          | 42HP       | 255.5mm | 1                | 156.8mm       | 219mm        |
| 24571-065     | 4U          | 42HP       | 315.5mm | 1                | 156.8mm       | 219mm        |
| 24571-066     | 4U          | 42HP       | 375.5mm | 1                | 156.8mm       | 219mm        |
| 24571-074     | 4U          | 63HP       | 255.5mm | 1                | 156.8mm       | 326mm        |
| 24571-077     | 4U          | 63HP       | 315.5mm | 1                | 156.8mm       | 326mm        |
| 24571-078     | 4U          | 63HP       | 375.5mm | 1                | 156.8mm       | 326mm        |
| 24571-086     | 4U          | 84HP       | 255.5mm | 1                | 156.8mm       | 432mm        |
| 24571-089     | 4U          | 84HP       | 315.5mm | 1                | 156.8mm       | 432mm        |
| 24571-090     | 4U          | 84HP       | 375.5mm | 1                | 156.8mm       | 432mm        |
| 24571-091     | 4U          | 84HP       | 435.5mm | 1                | 156.8mm       | 432mm        |
| 24571-092     | 4U          | 84HP       | 495.5mm | 1                | 156.8mm       | 432mm        |
| 24571-098     | 6U          | 28HP       | 255.5mm | 1                | 245.7mm       | 148mm        |
| 24571-101     | 6U          | 28HP       | 315.5mm | 1                | 245.7mm       | 148mm        |
| 24571-110     | 6U          | 42HP       | 255.5mm | 1                | 245.7mm       | 219mm        |
| 24571-113     | 6U          | 42HP       | 315.5mm | 1                | 245.7mm       | 219mm        |

| CatalogNumber | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|---------------|-------------|------------|---------|------------------|---------------|--------------|
| 24571-114     | 6U          | 42HP       | 375.5mm | 1                | 245.7mm       | 219mm        |
| 24571-122     | 6U          | 63HP       | 255.5mm | 1                | 245.7mm       | 326mm        |
| 24571-125     | 6U          | 63HP       | 315.5mm | 1                | 245.7mm       | 326mm        |
| 24571-126     | 6U          | 63HP       | 375.5mm | 1                | 245.7mm       | 326mm        |
| 24571-134     | 6U          | 84HP       | 255.5mm | 1                | 245.7mm       | 432mm        |
| 24571-137     | 6U          | 84HP       | 315.5mm | 1                | 245.7mm       | 432mm        |
| 24571-138     | 6U          | 84HP       | 375.5mm | 1                | 245.7mm       | 432mm        |
| 24571-139     | 6U          | 84HP       | 435.5mm | 1                | 245.7mm       | 432mm        |
| 24571-140     | 6U          | 84HP       | 495.5mm | 1                | 245.7mm       | 432mm        |
| 24572-117     | 5U          | 28HP       | 255.5mm | 1                | 201.25mm      | 148mm        |
| 24572-120     | 5U          | 28HP       | 315.5mm | 1                | 201.25mm      | 148mm        |
| 24572-129     | 5U          | 42HP       | 255.5mm | 1                | 201.25mm      | 219mm        |
| 24572-132     | 5U          | 42HP       | 315.5mm | 1                | 201.25mm      | 219mm        |
| 24572-133     | 5U          | 42HP       | 375.5mm | 1                | 201.25mm      | 219mm        |
| 24572-141     | 5U          | 63HP       | 255.5mm | 1                | 201.25mm      | 326mm        |
| 24572-144     | 5U          | 63HP       | 315.5mm | 1                | 201.25mm      | 326mm        |
| 24572-145     | 5U          | 63HP       | 375.5mm | 1                | 201.25mm      | 326mm        |
| 24572-153     | 5U          | 84HP       | 255.5mm | 1                | 201.25mm      | 432mm        |

| CatalogNumber | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|---------------|-------------|------------|---------|------------------|---------------|--------------|
| 24572-156     | 5U          | 84HP       | 315.5mm | 1                | 201.25mm      | 432mm        |
| 24572-157     | 5U          | 84HP       | 375.5mm | 1                | 201.25mm      | 432mm        |
| 24572-158     | 5U          | 84HP       | 435.5mm | 1                | 201.25mm      | 432mm        |
| 24572-159     | 5U          | 84HP       | 495.5mm | 1                | 201.25mm      | 432mm        |
| 24572-261     | 5U          | 28HP       | 255.5mm | 1                | 201.25mm      | 148mm        |
| 24572-264     | 5U          | 28HP       | 315.5mm | 1                | 201.25mm      | 148mm        |
| 24572-273     | 5U          | 42HP       | 255.5mm | 1                | 201.25mm      | 219mm        |
| 24572-276     | 5U          | 42HP       | 315.5mm | 1                | 201.25mm      | 219mm        |
| 24572-277     | 5U          | 42HP       | 375.5mm | 1                | 201.25mm      | 219mm        |
| 24572-285     | 5U          | 63HP       | 255.5mm | 1                | 201.25mm      | 326mm        |
| 24572-288     | 5U          | 63HP       | 315.5mm | 1                | 201.25mm      | 326mm        |
| 24572-289     | 5U          | 63HP       | 375.5mm | 1                | 201.25mm      | 326mm        |
| 24572-297     | 5U          | 84HP       | 255.5mm | 1                | 201.25mm      | 432mm        |
| 24572-300     | 5U          | 84HP       | 315.5mm | 1                | 201.25mm      | 432mm        |
| 24572-301     | 5U          | 84HP       | 375.5mm | 1                | 201.25mm      | 432mm        |
| 24572-302     | 5U          | 84HP       | 435.5mm | 1                | 201.25mm      | 432mm        |
| 24572-303     | 5U          | 84HP       | 495.5mm | 1                | 201.25mm      | 432mm        |
| 24572-500     | 2U          | 28HP       | 255.5mm | 1                | 67.9mm        | 148mm        |

| CatalogNumber | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|---------------|-------------|------------|---------|------------------|---------------|--------------|
| 24572-503     | 2U          | 28HP       | 315.5mm | 1                | 67.9mm        | 148mm        |
| 24572-510     | 2U          | 42HP       | 255.5mm | 1                | 67.9mm        | 219mm        |
| 24572-513     | 2U          | 42HP       | 315.5mm | 1                | 67.9mm        | 219mm        |
| 24572-514     | 2U          | 42HP       | 375.5mm | 1                | 67.9mm        | 219mm        |
| 24572-520     | 2U          | 63HP       | 255.5mm | 1                | 67.9mm        | 326mm        |
| 24572-523     | 2U          | 63HP       | 315.5mm | 1                | 67.9mm        | 326mm        |

Table 2/3

| Catalog Number | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height | Material |
|----------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|--------|----------|
| 24572-524      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-530      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-533      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-534      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |

| CatalogNumber | Front Frame Construction       | Cooling Option | Complies With                                                             | Finish                       | Height  | Material |
|---------------|--------------------------------|----------------|---------------------------------------------------------------------------|------------------------------|---------|----------|
| 24572-535     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 88.1mm  | Aluminum |
| 24572-536     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 88.1mm  | Aluminum |
| 24571-002     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |
| 24571-005     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |
| 24571-014     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |
| 24571-017     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |
| 24571-018     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24571-026     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-029     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-030     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-038     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-041     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-042     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |
| 24571-043     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6mm | Aluminum |

| CatalogNumber | Front Frame Construction       | Cooling Option | Complies With                                                             | Finish                       | Height  | Material |
|---------------|--------------------------------|----------------|---------------------------------------------------------------------------|------------------------------|---------|----------|
| 24571-044     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 132.6mm | Aluminum |
| 24571-050     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |
| 24571-053     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |
| 24571-062     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |
| 24571-065     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |
| 24571-066     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |
| 24571-074     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 177mm   | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|--------|----------|
| 24571-077     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-078     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-086     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-089     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-090     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-091     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |
| 24571-092     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 177mm  | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24571-098     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-101     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-110     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-113     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-114     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-122     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-125     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24571-126     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-134     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-137     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-138     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-139     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24571-140     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24572-117     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |

| CatalogNumber | Front Frame Construction       | Cooling Option | Complies With                                                             | Finish                       | Height  | Material |
|---------------|--------------------------------|----------------|---------------------------------------------------------------------------|------------------------------|---------|----------|
| 24572-120     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-129     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-132     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-133     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-141     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-144     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |
| 24572-145     | Side Trim,<br>Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated,<br>Powder Coated | 221.5mm | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24572-153     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-156     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-157     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-158     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-159     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-261     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-264     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24572-273     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-276     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-277     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-285     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-288     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-289     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-297     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24572-300     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-301     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-302     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-303     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 221.5mm | Aluminum |
| 24572-500     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm  | Aluminum |
| 24572-503     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm  | Aluminum |
| 24572-510     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm  | Aluminum |

| CatalogNumber | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height | Material |
|---------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|--------|----------|
| 24572-513     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-514     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-520     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |
| 24572-523     | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 88.1mm | Aluminum |

Table 3/3

| Catalog Number | Protection Rating | Static Load | Width   | Quick Ship |
|----------------|-------------------|-------------|---------|------------|
| 24572-524      | IP20              | 25kg        | 342.4mm | No         |
| 24572-530      | IP20              | 25kg        | 448.9mm | No         |
| 24572-533      | IP20              | 25kg        | 448.9mm | No         |
| 24572-534      | IP20              | 25kg        | 448.9mm | No         |
| 24572-535      | IP20              | 25kg        | 448.9mm | No         |
| 24572-536      | IP20              | 25kg        | 448.9mm | No         |
| 24571-002      | IP20              | 25kg        | 164.4mm | No         |

| Catalog Number | Protection Rating | Static Load | Width   | Quick Ship |
|----------------|-------------------|-------------|---------|------------|
| 24571-005      | IP20              | 25kg        | 164.4mm | No         |
| 24571-014      | IP20              | 25kg        | 235.5mm | No         |
| 24571-017      | IP20              | 25kg        | 235.5mm | No         |
| 24571-018      | IP20              | 25kg        | 235.5mm | No         |
| 24571-026      | IP20              | 25kg        | 342.4mm | No         |
| 24571-029      | IP20              | 25kg        | 342.4mm | No         |
| 24571-030      | IP20              | 25kg        | 342.4mm | No         |
| 24571-038      | IP20              | 25kg        | 448.9mm | No         |
| 24571-041      | IP20              | 25kg        | 448.9mm | No         |
| 24571-042      | IP20              | 25kg        | 448.9mm | No         |
| 24571-043      | IP20              | 25kg        | 448.9mm | No         |
| 24571-044      | IP20              | 25kg        | 448.9mm | No         |
| 24571-050      | IP20              | 25kg        | 164.4mm | No         |
| 24571-053      | IP20              | 25kg        | 164.4mm | No         |
| 24571-062      | IP20              | 25kg        | 235.5mm | No         |
| 24571-065      | IP20              | 25kg        | 235.5mm | No         |
| 24571-066      | IP20              | 25kg        | 235.5mm | No         |
| 24571-074      | IP20              | 25kg        | 342.4mm | No         |

| Catalog Number | Protection Rating | Static Load | Width   | Quick Ship |
|----------------|-------------------|-------------|---------|------------|
| 24571-077      | IP20              | 25kg        | 342.4mm | No         |
| 24571-078      | IP20              | 25kg        | 342.4mm | No         |
| 24571-086      | IP20              | 25kg        | 448.9mm | No         |
| 24571-089      | IP20              | 25kg        | 448.9mm | No         |
| 24571-090      | IP20              | 25kg        | 448.9mm | No         |
| 24571-091      | IP20              | 25kg        | 448.9mm | No         |
| 24571-092      | IP20              | 25kg        | 448.9mm | No         |
| 24571-098      | IP20              | 25kg        | 164.4mm | No         |
| 24571-101      | IP20              | 25kg        | 164.4mm | No         |
| 24571-110      | IP20              | 25kg        | 235.5mm | No         |
| 24571-113      | IP20              | 25kg        | 235.5mm | No         |
| 24571-114      | IP20              | 25kg        | 235.5mm | No         |
| 24571-122      | IP20              | 25kg        | 342.4mm | No         |
| 24571-125      | IP20              | 25kg        | 342.4mm | No         |
| 24571-126      | IP20              | 25kg        | 342.4mm | No         |
| 24571-134      | IP20              | 25kg        | 448.9mm | No         |
| 24571-137      | IP20              | 25kg        | 448.9mm | No         |
| 24571-138      | IP20              | 25kg        | 448.9mm | No         |

| Catalog Number | Protection Rating | Static Load | Width   | Quick Ship |
|----------------|-------------------|-------------|---------|------------|
| 24571-139      | IP20              | 25kg        | 448.9mm | No         |
| 24571-140      | IP20              | 25kg        | 448.9mm | No         |
| 24572-117      | IP20              | 25kg        | 164.4mm | No         |
| 24572-120      | IP20              | 25kg        | 164.4mm | No         |
| 24572-129      | IP20              | 25kg        | 235.5mm | No         |
| 24572-132      | IP20              | 25kg        | 235.5mm | No         |
| 24572-133      | IP20              | 25kg        | 235.5mm | No         |
| 24572-141      | IP20              | 25kg        | 342.4mm | No         |
| 24572-144      | IP20              | 25kg        | 342.4mm | No         |
| 24572-145      | IP20              | 25kg        | 342.4mm | No         |
| 24572-153      | IP20              | 25kg        | 448.9mm | No         |
| 24572-156      | IP20              | 25kg        | 448.9mm | No         |
| 24572-157      | IP20              | 25kg        | 448.9mm | No         |
| 24572-158      | IP20              | 25kg        | 448.9mm | No         |
| 24572-159      | IP20              | 25kg        | 448.9mm | No         |
| 24572-261      | IP20              | 25kg        | 164.4mm | No         |
| 24572-264      | IP20              | 25kg        | 164.4mm | No         |
| 24572-273      | IP20              | 25kg        | 235.5mm | No         |

| Catalog Number | Protection Rating | Static Load | Width   | Quick Ship |
|----------------|-------------------|-------------|---------|------------|
| 24572-276      | IP20              | 25kg        | 235.5mm | No         |
| 24572-277      | IP20              | 25kg        | 235.5mm | No         |
| 24572-285      | IP20              | 25kg        | 342.4mm | No         |
| 24572-288      | IP20              | 25kg        | 342.4mm | No         |
| 24572-289      | IP20              | 25kg        | 342.4mm | No         |
| 24572-297      | IP20              | 25kg        | 448.9mm | No         |
| 24572-300      | IP20              | 25kg        | 448.9mm | No         |
| 24572-301      | IP20              | 25kg        | 448.9mm | No         |
| 24572-302      | IP20              | 25kg        | 448.9mm | No         |
| 24572-303      | IP20              | 25kg        | 448.9mm | No         |
| 24572-500      | IP20              | 25kg        | 164.4mm | No         |
| 24572-503      | IP20              | 25kg        | 164.4mm | No         |
| 24572-510      | IP20              | 25kg        | 235.5mm | No         |
| 24572-513      | IP20              | 25kg        | 235.5mm | No         |
| 24572-514      | IP20              | 25kg        | 235.5mm | No         |
| 24572-520      | IP20              | 25kg        | 342.4mm | No         |
| 24572-523      | IP20              | 25kg        | 342.4mm | No         |

ADDITIONAL PRODUCT DETAILS

- Modifications (special colours or sizes).
- Custom solutions (cut-outs in top cover, base plate or side panels).
- Assembly service from 1 piece.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE