

# nVent CADDY Speed Link SLK Locking Device



## CERTIFICATIONS



## FEATURES

Push/pull keyless release allows easy adjustments

Low-profile locking device minimizes visual impact

Cable spread of 90 degrees allows positioning the device closer to the load

Keyless release tubes are easy to operate while wearing gloves

Double-sided locking mechanism enables simple height adjustment

## SPECIFICATIONS

**Material:** Steel;Polypropylene;Zinc Alloy

Table 1/2

| Catalog Number | Article Number | Wire Rope Diameter | Height (H) | Width (W) | Thickness (T) | Angle (a) |
|----------------|----------------|--------------------|------------|-----------|---------------|-----------|
| SLK2C200       | 196600         | 1.5 - 2 mm         | 55 mm      | 19 mm     | 12.5 mm       | 90 ° Max  |
| SLK2R10        | 196770         | 1.5 - 2 mm         | 55 mm      | 19 mm     | 12.5 mm       | 90 ° Max  |

| CatalogNumber | Article Number | Wire Rope Diameter | Height (H) | Width (W) | Thickness (T) | Angle (a) |
|---------------|----------------|--------------------|------------|-----------|---------------|-----------|
| SLK3C200      | 196730         | 3 mm               | 62 mm      | 24 mm     | 16 mm         | 90 ° Max  |


Table 2/2

| Catalog Number | Article Number | Certifications |
|----------------|----------------|----------------|
| SLK2C200       | 196600         | UL, cUL, ITB   |
| SLK2R10        | 196770         | UL, cUL, ITB   |
| SLK3C200       | 196730         |                |

## ADDITIONAL PRODUCT DETAILS

Locking devices are only to be used with nVent CADDY Speed Link wire spools and accessories with the same specified Wire Rope Diameter as the locking device. Do not use with any other wires.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

