


Hydraulic Flexible/Non-Flexible Busbar Bender



CERTIFICATIONS



FEATURES

Works with copper or aluminium busbar and nVent ERIFLEX Flexibar

Multi-function tool creates "V" or "Z" bends and straightens busbar for corrections

Removable top plate allows for multiple bends on a busbar

Bottom plate is etched to indicate a 90° bend

Includes steel bar supports for bending busbar when tool is not fixed to the Hydraulic nVent ERIFLEX Flexibar and Busbar Work Center

RoHS compliant

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Busbar Width	Busbar Thickness	Bending Angle	Bending Radius	Depth (D)
HYDR-BB-BEN	545670	200 mm Max	12.7 mm Max	100 ° Max	12.5mm	500mm

Table 2/2

Catalog Number	Article Number	Height (H)	Width (W)	Unit Weight
----------------	----------------	------------	-----------	-------------

HYDR-BB-BEN	545670	261 mm	230 mm	51 kg
-------------	--------	--------	--------	-------

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE