

DECLARATION OF COMPLIANCE

REACH SVHC (EC 1907/2006)

In accordance with nVent's ESG commitments and article 33 of EC 1907/2006, we continuously strive to deliver products and services that reduce environmental and health and safety impacts when used for their intended purpose and in accordance with the performance conditions stated in our product documentation.

nVent declares to the best of our knowledge, based on supplier responses or our own ongoing due diligence, that our products and packaging are manufactured in compliance with the REACH regulation (EC 1907/2006). The presence of any substance specified in the REACH ECHA Substances of Very High Concern (SVHC) candidate list (<https://echa.europa.eu/candidate-list-table>) in nVent products is set out in the attached table.

Because we know regulations, standards and available information continues to evolve, nVent closely monitors, investigates, communicates, and exercises ongoing due diligence within our supply chain to ensure we continue to meet our obligations under the REACH SVHC Regulation. In the event that nVent becomes aware of the presence of a substance on the SVHC list, whether through investigation, testing, or notification from a supplier, we will promptly notify appropriate authorities under the regulation and amend the attached table to reflect the same.

Regards,



Tom Hurney

Director, Enterprise Product Compliance & Approvals


CADDY | ERICO | HOFFMAN | RAYCHEM | SCHROFF | TRACER

nVent has identified the following products/articles that contain substances of very high concern (SVHC) as listed on the ECHA candidate list at levels exceeding the threshold limit value of 0.1% weight by weight (w/w). This table will be updated as new information warrants.

Product Description	Product Part Number	SVHC Name	CAS No.
Cleaner for stainless steel	SSC01 Mixtures: Innoshine B570 & Innocare B580 REACH, annex XVII: Entry 3, Entry 40, Entry 75		
ComLine Ground Buss	EGBB1, EGBB2	Dimethyl phthalate	131-11-3
LED Light	AALGT10, EL1200D24V, EL1200DS, EL1200M, EL1200M24V, EL1200MS, EL900D, EL900DS	Lead	7439-92-1
Compression Lugs	DGCL21, DGCL61	Lead	7439-92-1
Window Kit	LWHD1616, LWHD2525, APWKE133, APWKE52, APWKE96	Dimethyl Phthalate	131-11-3
Door-Mount PDU 4.3-inch LCD Display	LCD4INDRMT	Lead	7439-92-1
Express Rack Top Baffle	UACTB6A, UACTB6V, UACTB7A, UACTB7V, UACTB75A, UACTB75V, UACTB8A, UACTB8V	Dimethyl Phthalate	131-11-3
Express Transom Window	UACTW4B, UACTW6B	Dimethyl Phthalate	131-11-3
Extension frame	OPCP202006EE, OPCP203006EE, OPCP204006EE, OPCP303006EE, OPCP304006EE, OPCP306006EE, OPCP406006EE	Dimethyl Phthalate	131-11-3
H2Omit Vent Drain	AVDR4NM	Dimethyl Phthalate	131-11-3
Heavy-Duty C-Taps	DGT1, DGT2	Lead	7439-92-1
Ground Bar Kit	DG19, DG23, DG36, DG72	Lead	7439-92-1
Hot Aisle Return Plenum	PCPPS1200, PCPPE48, PCPPS600, PCPPS750, PCPPS800	Dimethyl Phthalate	131-11-3
Inner cover plate	UFCP1080, UFCP1081, UFCP1082, UFCP3200, UFCP3201, UFCP4300, UFCP4301, UFCP4302, UFCP5400, UFCP5401, UFCP5402, UFCP6400, UFCP6401, UFCP6402, UFCP7500, UFCP7501, UFCP7502, UFCP8600, UFCP8601, UFCP8602	Dimethyl Phthalate	131-11-3
Insulated Ground Jumper Kit	DGJ, DGRJ	Lead	7439-92-1
InterSafe Data Interface Polycarbonate	HGF5USBUSBCC, HDP5CNCC, HGF5CNCC, HDP58MDHCC, HGF58MDHCC, HDP5ETHDHCC, HGF5ETHDHCC, HDP5ETHETHCC,	Dimethyl phthalate, Lead	131-11-3, 7439-92-1

	HGF5ETHETHCC, HDP5ETHCC, HGF5ETHCC, HDP5PBCC		
InterSafe Data Interface Port	HDP5CNSS, HGF5CN, HGF5CNSS, HDP58MDH, HDP58MDHSS, HGF58MDH, HGF58MDHSS, HDP5ETHDHSS, HDP5ETHDH, HGF5ETHDHSS, HGF5ETHDH, HDP5ETHETH, HDP5ETHETHSS, HGF5ETHETH, HGF5ETHETHSS, HDP5ETH, HDP5ETHSS, HGF5ETH, HGF5ETHSS, HDP5PB, HGF5PB, HGF5PBSS	Lead	7439-92-1
MODO Filter	MDACFTCF5100S, MDACFTCF5200S	Dimethyl Phthalate	131-11-3
Oil Chiller	TAOA1,TAOA3, TAOA5, TAOA8, TAOB5, TAOB9,TAOC5, TAOD0, TAOD9, TAOE6, TAOF8	Difluoromethane Pentafluoroethane	75-10-5 354-33-6
Panel-Mount Fan Speed Controls	AFANTSC	Dimethyl Phthalate	131-11-3
PolyPro Hinge Retainers	AHGCLP	Dimethyl Phthalate	131-11-3
Mounting Brackets	APOLYFT10, APOLYFT12, APOLYFT14, APOLYFT16, APOLYFT4, APOLYFT6, APOLYFT8, QEMFK, QIMFK, SFL1E, QDMFK, DFL1E	Dimethyl Phthalate	131-11-3
PolyPro Polyester Enclosures	A10106PHC, A1084PHC, A12106PHC, A14128PHC, A16148PHC, A181610PHC, A644PHC, A664PHC, A864PHC, A884PHC, D16148WFW, D664WFW, D16148WF, D664WF, A10106PHCW, A1084PHCW, A12106PHCW, A14128PHCW, A16148PHCW, A181610PHCW, A644PHCW, A664PHCW, A864PHCW, A884PHCW	Dimethyl Phthalate	131-11-3
QLine Enclosures	Q1286PCEMC, Q1289PCEMC, Q16129PCEMC, Q1689PCEMC, Q20129PCEMC, Q24169PCEMC, Q302311HDWKIT, Q1PBPCDM, Q1PBPCD, Q2PBPCDM, Q2PBPCD, Q3PBPCDM, Q3PBPCD, Q4PBPCDM, Q4PBPCD, Q6PBPCD, Q13138PCEMC, Q131310PCEMC, Q1388PCEMC, Q18138PCEMC, Q181310PCEMC, Q18188PCEMC, Q13810ABECC, Q202013PCEMC, Q302013PCEMC, Q402013PCEMC, Q202018ABICC, Q202018PCICC, Q302018ABICC, Q302018PCICC, Q303018ABICC, Q303018PCICC, Q402018ABICC, Q402018PCICC, Q403018ABICC, Q403018PCICC, Q603018ABICC, Q603018PCICC, Q604018ABICC, Q604018PCICC, Q202013PCIQRCCR, Q202018PCIQRCCR, Q302013PCIQRCCR, Q302018PCIQRCCR, Q303013PCIQRCCR, Q303018PCIQRCCR, Q402013PCIQRCCR, Q402018PCIQRCCR, Q403013PCIQRCCR, Q403018PCIQRCCR, Q603013PCIQRCCR, Q603018PCIQRCCR, Q604013PCIQRCCR, Q604018PCIQRCCR, Q202013PCIQRR, Q202018PCIQRR, Q302013PCIQRR, Q302018PCIQRR,	Dimethyl Phthalate	131-11-3

	Q303013PCIQRR, Q303018PCIQRR, Q402013PCIQRR, Q402018PCIQRR, Q403013PCIQRR, Q403018PCIQRR, Q603013PCIQRR, Q603018PCIQRR, Q604013PCIQRR, Q604018PCIQRR, Q202018ABI, Q202018PCI, Q302013PCI, Q302018ABI, Q302018PCI, Q303018ABI, Q303018PCI, Q402018ABI, Q402018PCI, Q403018ABI, Q403018PCI, Q603018ABI, Q603018PCI, Q604018ABI, Q604018PCI		
Quiet Vortex Cooler	VA1516012, VA2516012, VA5016012, VA0916012, VA151604X, VA251604X, VA501604X, VA091604X	Dimethyl Phthalate	131-11-3
Rack- and Panel-Mount PDU	DP1N191015S, DP1N191020ST, DP1N191020S, DP1N191020, DP1N191415, DP1N481815, DP1N622415, DP1N622420T DP1N622420, DP1N190615, DP1N160620S	Lead	7439-92-1
RackChiller Coolant Distribution Unit	CDU1002R001Q, CDU1002R001, CDU0402R001Q, CDU0402R001, CDU8004LA03B, CDU8004LA03A	Lead	7439-92-1
RJ Solar Box	RJ-1, RU-1-LP, RU-2-LP	Dimethyl Phthalate	131-11-3
Small Polycarbonate Terminal Box	DPCP121206TE, DPCP121209TE, DPCP121609TE, DPCP122009TE, DPCP152008TE, DPCP162412TE, DPCP162409TE, DPCP233011TE, DPCP233009TE, DPCP050504TE, DPCP050704TE, DPCP081206TE, DPCP081209TE, DPCP081606TE, DPCP081609TE, DPCP080806TE, DPCP080809TE	Dimethyl Phthalate	131-11-3
Switched PDU Outlet and Environmental Monitor	DPC1N119820	Lead	7439-92-1
Telecommunications Ground Bar Kits	DGTB212, DGTB216, DGTB412	Lead	7439-92-1
Terminal boxes	Q12126ABDCC, DPCP121206GE, Q12126PCD, Q12126PCDCC, Q12129ABDCC, DPCP121209GE, Q12129PCD, Q12129PCDCC, MGRP121209GE, Q16129ABDCC, DPCP121609GE, Q16129PCD, Q16129PCDCC, Q20129ABDCC, DPCP122009GE, Q20129PCD, Q20129PCDCC, MGRP122209GE, Q131310ABECC, Q131310PCE, Q131310PCECC, Q131313ABECC, Q131313PCE, Q131313PCECC Q13138ABECC, Q13138PCE, Q13138PCECC Q181310ABECC, Q181310PCE Q181310PCECC, Q181313ABECC Q181313PCE, Q181313PCECC Q181315ABECC, Q181315PCE Q181315PCECC, Q18138ABECC, Q18138PCE Q18138PCECC, Q20158ABDCC DPCP152008GE, Q20158PCD, Q20158PCDCC	Dimethyl Phthalate	131-11-3

	MGRP161609GE, Q241612ABDCC DPCP162412GE, Q241612PCD Q241612PCDCC, Q24169ABDCC DPCP162409GE, Q24169PCD, Q24169PCDCC MGRP162609GE, MGRP163609GE MGRP165609GE, Q181810ABECC Q181810PCE, Q181810PCECC Q181813ABECC, Q181813PCE Q181813PCECC, Q181815ABECC Q181815PCE, Q181815PCECC, Q18188ABECC Q18188PCE, Q18188PCECC, Q251810ABECC Q251810PCE, Q251810PCECC Q251815ABECC, Q251815PCE Q251815PCECC, Q25188ABECC, Q25188PCE Q25188PCECC, OPCP202013GE Q202013PCI, Q202013PCICC, OPCP202013TE Q202013ABICC, OPCP203013GE Q302013PCICC, OPCP203013TE Q302013ABICC, OPCP204013GE, Q402013PCI Q402013PCICC, OPCP204013TE Q402013ABICC, Q302311ABDCC DPCP233011GE, Q302311PCD Q302311PCDCC, Q30239ABDCC DPCP233009GE, Q30239PCD, Q30239PCDCC MGRP252612GE, MGRP254012GE OPCP303013GE, Q303013PCI, Q303013PCICC OPCP303013TE, Q303013ABICC OPCP304013GE, Q403013PCI, Q403013PCICC OPCP304013TE, Q403013ABICC OPCP306013GE, Q603013PCI, Q603013PCICC OPCP306013TE, Q603013ABICC OPCP406013GE, Q604013PCI, Q604013PCICC OPCP406013TE, Q604013ABICC MGRP414012GE, Q554ABDCC DPCP050504GE, Q554PCD, Q554PCDCC DPCP050704GE, MGRP081106GE MGRP081108GE, Q13810PCE, Q13810PCECC Q13813ABECC, Q13813PCE, Q13813PCECC Q1388ABECC, Q1388PCE, Q1388PCECC MGRP081606GE, MGRP081608GE MGRP081906GE, MGRP081908GE MGRP080806GE, MGRP080808GE Q1286ABDCC, DPCP081206GE Q1286PCD, Q1286PCDCC, Q1289ABDCC DPCP081209GE, Q1289PCD, Q1289PCDCC Q1686ABDCC, DPCP081606GE, Q1686PCD Q1686PCDCC, Q1689ABDCC, DPCP081609GE Q1689PCD, Q1689PCDCC, Q886ABDCC DPCP080806GE, Q886PCD, Q886PCDCC Q889ABDCC, DPCP080809GE, Q889PCD Q889PCDCC		
Thermostat Controller	THERM16C, THERM16F, THERM26C THERM26F	Lead	7439-92-1
Ultrix Grounding Device	UUGK	Dimethyl Phthalate	131-11-3
Window Kit	95HCD, SW32, SW44, SW64, SW84N, SW84X SW97, VM-CTHS23, VM-CTHS43, VM-CTHS53 VM-CTHS73, APWK116NFNM, APWK138NFNM APWK53NFNM, APWK95NFNM	Dimethyl Phthalate	131-11-3

Screw Cover	VM754H, VM433, VM533, VM534, VM553 VM554, VM733, VM753, VM754, VM755, VM773 VM775, VM776, VM933, VM533K, VM534K VM553K, VM554K, VM753K, VM754K, VM755K VM773K, VM775K, VM776K, VM533CTH VM534CTH, VM754CTH, VM533CT, VM534CT VM553CT, VM554CT, VM753CT, VM754CT VM755CT, VM773CT, VM775CT, VM776CT VM533CTK, VM534CTK, VM553CTK VM554CTK, VM753CTK, VM754CTK VM755CTK, VM773CTK, VM775CTK VM776CTK, VM433-PBM1, VM433-PBS1 VM533-PBM2, VM733-PBM3, VM733-PBS1 VM733-PBS2, VM755-PBM6, VM755-PBS4 VM775-PBM4, VM775-PBM6, VM775-PBM9 VM775-PBS4, VM933-PBM4, VM933-PBM5 VM933-PBS3	Dimethyl Phthalate	131-11-3
A/C Enclosure	VHL15160, VHL25160, VHL50160, VHL09160	Dimethyl Phthalate	131-11-3
Air Filter	VAAF15, VAAF50	Dimethyl Phthalate	131-11-3
Oil Filter	VCOF17, VCOF25	Dimethyl Phthalate	131-11-3
Wall mounted Enclosure	UDP100100,UDP100102, UDP100125 UDPT10050, UDP10050, UDPT10075 UDP10075, UCPT1080, UCP1080, UDP125100 UDP125102, UDPT12575, UDP12575, UCP320 UCPT430, UCP430, UDPT5050, UDP5050 UDPT5075, UDP5075, UCPT540, UCP540 UCPT640, UCP640, UCPT750, UCP750 UDP75100, UDP75125, UDPT7550, UDP7550 UDPT7575, UDP7575, UCPT860, UCP860	Dimethyl Phthalate	131-11-3
Water Chiller	TALM0, TALA1, TALA3, TALO6, TALA5, TALA8 TALB5, TALB9, TALC5, TALD0, TALD9, TALE6 TALF8, TALG9, TALI4	Difluoromethane Pentafluoroethane	75-10-5 354-33-6

Last Updated: July 2025