


# Front Panel Kit, Unshielded, Bottom Hinged, 3 U, 84 HP

## Power Utilities

### CATALOG NUMBER

**20838-273**



Unshielded front panel bottom hinged.

### CERTIFICATIONS



### FEATURES

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

### PRODUCT ATTRIBUTES

Product Type: Front Panel

Type: Front Panel without Handle

Mounting: Hinged, Bottom

EMC Shielding: No

Material: Aluminum

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: No

Rack Height: 3 U

Height: 128.4 mm

Rack Width: 84 HP

Width: 426.4 mm

Complies With: IEC 60297-3-101; IEEE 1101.1/10

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

---

Front panel can be removed in opened position (> 135°).

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE