

# Varistar CP Steel Door, Perforated With 1-Point Locking

## Power Utilities

Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

### FEATURES

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Locking Type         | Color      | Color Code |
|----------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-408      | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-409      | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-507      | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-508      | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-410      | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-411      | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-509      | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Locking Type         | Color      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-510     | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-412     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-413     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-511     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-512     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-414     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-415     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-513     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-514     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-006     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-013     | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-515     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-516     | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-007     | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-014     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-517     | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-518     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-008     | 52 U        | 2450 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Locking Type         | Color      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-015     | 52 U        | 2450 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Complies With            | Product Type | Protection Rating | Type                   | Works With  |
|----------------|--------------------------|--------------|-------------------|------------------------|-------------|
| 21630-408      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-409      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-507      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-508      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-410      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-411      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-509      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-510      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-412      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-413      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-511      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-512      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-414      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-415      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-513      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-514      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

| Catalog Number | Complies With            | Product Type | Protection Rating | Type                   | Works With  |
|----------------|--------------------------|--------------|-------------------|------------------------|-------------|
| 21630-006      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-013      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-515      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-516      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-007      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-014      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-517      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-518      | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-008      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-015      | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**