

PEMSA Wire Basket Tray C Bracket



CERTIFICATIONS







FEATURES

Easy to use, quick connect feature

Ideal for ceiling, wall and channel installations

Side load access for cable installation

IEC 61537 load rating and earthing compliant

SPECIFICATIONS


Finish: Electrogalvanized

Material: Steel

Table 1/1									
Catalog Number	Article Number	Length 1 (L1)	Length 2 (L2)	Width (W)	Height (H)	Static Load			
WBT200CBRKT	820330	137 mm	265 mm	54 mm	190 mm	284N			
WBT100CBRKT	820310	137 mm	165 mm	54 mm	190 mm	327N			

CatalogNumber	Article Number	Length 1 (L1)	Length 2 (L2)	Width (W)	Height (H)	Static Load
WBT300CBRKT	820340	137 mm	365 mm	54 mm	190 mm	245N
WBT400CBRKT	820350	137 mm	465 mm	54 mm	190 mm	177N
WBT150CBRKT	820320	137 mm	200 mm	54 mm	190 mm	353N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HO

HOFFMAN

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.