

# SOSR Stand Off Two Hole Strap for CPVC Pipe



## CERTIFICATIONS



## FEATURES

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Positions pipe 1-1/2" (38 mm) off the mounting surface eliminating the need for wooden spacer blocks

Can be mounted in both vertical and horizontal positions on concrete, steel and wood

Meets the UL® 203 stringent upward thrust requirement

UL® Listed as both a hanger and pipe restraint

Complies with static load requirements of NFPA® 13

Includes mounting screws

Can be used with 3TW backing nut on composite wood joist installations

## SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Steel


Table 1/2

| Catalog Number | Article Number | NB/DN | Hole Size (HS) | A      | B      | C       |
|----------------|----------------|-------|----------------|--------|--------|---------|
| SOSR200        | 597809         | 50    | 5.1 mm         | 102 mm | 133 mm | 25.4 mm |
| SOSR150        | 597808         | 40    | 5.1 mm         | 98 mm  | 114 mm | 25.4 mm |
| SOSR100        | 597806         | 25    | 5.1 mm         | 75 mm  | 94 mm  | 25.4 mm |
| SOSR125        | 597807         | 32    | 5.1 mm         | 84 mm  | 92 mm  | 25.4 mm |
| SOSR075        | 597805         | 20    | 5.1 mm         | 68 mm  | 92 mm  | 25.4 mm |

Table 2/2

| Catalog Number | Article Number | Thickness (T) | Hanger Spacing |
|----------------|----------------|---------------|----------------|
| SOSR200        | 597809         | 1.61 mm       | 2.4 m Max      |
| SOSR150        | 597808         | 1.61 mm       | 2.1 m Max      |
| SOSR100        | 597806         | 1.3 mm        | 1.8 m Max      |
| SOSR125        | 597807         | 1.61 mm       | 1.95 m Max     |
| SOSR075        | 597805         | 1.3 mm        | 1.65 m Max     |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

