

Telecom Main Grounding Busbar

Data Solutions



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 6.35mm
Width (W): 101.6mm
Material: Copper


Table 1/2

Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	A
----------------	-------------	---------------	---------------	-----------------------------------	-----------------------------------	---

TMGBA12L15P	No	305mm	229mm	15	3	25.4mm
TMGBA12L15PT	Yes	305mm	229mm	15	3	25.4mm
TMGBA20L27P	No	508mm	229mm	27	3	25.4mm
TMGBA24L33PT	Yes	610mm	457mm	33	5	25.4mm

Table 2/2			
Catalog Number	B	C	D
TMGBA12L15P	28.6mm	15.9mm	15.9mm
TMGBA12L15PT	28.6mm	15.9mm	15.9mm
TMGBA20L27P	28.6mm	15.9mm	15.9mm
TMGBA24L33PT	28.6mm	15.9mm	15.9mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE