

# UFS nVent ERIFLEX Flexibar and IBSB Support Kit

## Power Utilities



### CERTIFICATIONS



### FEATURES

Kit includes one rail and 24 retaining blocks

Create up to three 650 mm (25.6") supports capable of holding four nVent ERIFLEX Flexibar

Retaining blocks are halogen free

RoHS compliant

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Conductor Thickness | Conductor Width | Height (H) | Width (W) | A     |
|----------------|----------------|---------------------|-----------------|------------|-----------|-------|
| UFS-KIT        | 553590         | 2 – 8 mm            | 15.5 – 120.0 mm | 57.50 mm   | 30 mm     | 24 mm |


Table 2/2

| Catalog Number | Article Number | B     | Unit Weight |
|----------------|----------------|-------|-------------|
| UFS-KIT        | 553590         | 15 mm | 2.300 kg    |

## ADDITIONAL PRODUCT DETAILS

Recommended distance between supports is 400 mm (15 3/4").

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**