

# IceStop Self-Regulating Heating Cable



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

## FEATURES

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

## SPECIFICATIONS

|                                      |                      |
|--------------------------------------|----------------------|
| <b>Nominal Thickness:</b>            | 6 mm                 |
| <b>Nominal Width:</b>                | 14 mm                |
| <b>Nominal Cable Weight:</b>         | 130 g/m              |
| <b>Supply Voltage:</b>               | 208 – 240 V          |
| <b>Min Installation Temperature:</b> | -18 °C               |
| <b>Color:</b>                        | Black                |
| <b>Ground Path Type:</b>             | Braid                |
| <b>Conductor Material:</b>           | Nickel-Plated Copper |

Table 1/1

| Catalog Number | Item Name | Nominal Power Output, In Air @ 0°C, 230V | Nominal Power Output, In Ice Water @ 0°C, 230V | Outer Jacket Material |
|----------------|-----------|------------------------------------------|------------------------------------------------|-----------------------|
| 446105-000     | GM-2X     | 18 W/m                                   | 36 W/m                                         | Modified Polyolefin   |

| Catalog Number | Item Name | Nominal PowerOutput,<br>In Air @ 0°C,230V | Nominal PowerOutput,<br>In Ice Water @0°C,<br>230V | Outer Jacket Material |
|----------------|-----------|-------------------------------------------|----------------------------------------------------|-----------------------|
| 092961-000     | GM-2XT    | 18 W/m                                    | 36 W/m                                             | Fluoropolymer         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT