

# SBS-R-FP Control Panel for Pipe Freeze Protection



## SPECIFICATIONS

<b>Phase Quantity:</b>	3
<b>IP Rating:</b>	IP65
<b>Protection:</b>	Miniature- / Earth Leakage Circuit Breaker
<b>Mounting:</b>	Wall Mounted
<b>Over Voltage Protection:</b>	Yes

Table 1/2

Catalog Number	Item Name	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA
1244-016626	SBS-R-FP-1X16A	1	1	16 A, Type C	40 A	1
1244-016627	SBS-R-FP-3X16A	1	3	16 A, Type C	40 A	1
1244-016629	SBS-R-FP-1X10A	1	1	10 A, Type C	40 A	1
1244-016630	SBS-R-FP-3X10A	1	3	10 A, Type C	40 A	1
1244-021775	SBS-R-FP-1X13A	1	3	13 A, Type C	40 A	1
1244-021776	SBS-R-FP-3X13A	1	3	13 A, Type C	40 A	1

CatalogNumber	Item Name	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA
1244-016628	SBS-R-FP-6X16A	2	6	16 A, Type C	40 A	2
1244-016631	SBS-R-FP-6X10A	2	6	10 A, Type C	40 A	2
1244-021777	SBS-R-FP-6X13A	2	6	13 A, Type C	40 A	2

Table 2/2

Catalog Number	Item Name	Height	Width	Depth	Housing Material
1244-016626	SBS-R-FP-1X16A	286 mm	418 mm	148 mm	Plastic
1244-016627	SBS-R-FP-3X16A	436 mm	418 mm	148 mm	Plastic
1244-016629	SBS-R-FP-1X10A	246 mm	310 mm	148 mm	Plastic
1244-016630	SBS-R-FP-3X10A	436 mm	418 mm	148 mm	Plastic
1244-021775	SBS-R-FP-1X13A	586 mm	310 mm	148 mm	Plastic
1244-021776	SBS-R-FP-3X13A	586 mm	310 mm	148 mm	Plastic
1244-016628	SBS-R-FP-6X16A	586 mm	418 mm	148 mm	Plastic
1244-016631	SBS-R-FP-6X10A	586 mm	418 mm	148 mm	Plastic
1244-021777	SBS-R-FP-6X13A	586 mm	600 mm	148 mm	Plastic

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,**

**Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**