

Intelligent PDU, EN2xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN2326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2317	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black
EN2316-A	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black
EN2350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C21	40	Black

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN2380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C21	32	Black
EN2325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN2337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

Table 2/6

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Length	Input Cable Location
EN2326	No Circuit Breaker	Yes	0	3.7 kVA	3m	Top Feed
EN2317	16 A, 1-pole, Hy-Mag	Yes	0			Top Feed
EN2316-A	16 A, 1-pole, Hy-Mag	Yes	0			Front Feed
EN2350	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2380	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2325	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2329	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2337	16 A, 1-pole, Hy-Mag	Yes	2			Top Feed

Table 3/6

Catalog Number	Input Voltage	Phase	Max Power Input	Nominal Voltage	On/Off Switch Included	Output Voltage
EN2326	100 – 240V	1 PH	3.68 kVA	230V	Yes	230VAC
EN2317	200 – 240V	1 PH	3.68 kVA			200 – 240VAC

CatalogNumber	Input Voltage	Phase	Max Power Input	Nominal Voltage	On/Off Switch Included	Output Voltage
EN2316-A	100 – 240V	1 PH	3.68 kVA			100 – 240VAC
EN2350	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2380	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2325	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2329	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2337	200 – 240V	1 PH	7.44 kVA			200 – 240VAC

Table 4/6

Catalog Number	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type	Material
EN2326	16 A	IEC 60309 316P6 (IP44)	0U	Yes	Input	Steel
EN2317	16 A	IEC 60309 316P6 (IP44)	0U	No	Input	
EN2316-A	20 A (16 A) North America, 16 A International	C20	0U	Yes	Input	
EN2350	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Steel
EN2380	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Steel
EN2325	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Steel
EN2329	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Steel
EN2337	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	

Table 5/6

Catalog Number	Finish	Height	Width	Depth	Weight	Package Quantity
----------------	--------	--------	-------	-------	--------	------------------

EN2326	Powder Coated	1490mm	52mm	53mm	7.21kg	1
EN2317						1
EN2316-A						1
EN2350	Powder Coated	1490mm	56mm	75mm	9.12kg	1
EN2380	Powder Coated	1490mm	56mm	75mm		1
EN2325	Powder Coated	1750mm	52mm	53mm	9.5kg	1
EN2329	Powder Coated	1750mm	52mm	53mm	8.52kg	1
EN2337						1

Table 6/6

Catalog Number	Interrupt Rating	Quick Ship
EN2326	5kAIC	No
EN2317	5kAIC	No
EN2316-A	5kAIC	No
EN2350	5kAIC	No
EN2380	5kAIC	No
EN2325	5kAIC	No
EN2329	5kAIC	No
EN2337	5kAIC	No

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE