

Plug-In Unit Front Panel for IEL, IET, Type 2 Handle



Flat front panel. It enables an assembly on IEL, IET or the type 2 handle in trapezoid form.

CERTIFICATIONS



FEATURES

Al, 2.5 mm, front anodized, Rear conductive; trapezium shaped handle, gray, PPE, UL 94 V-1

Front panel, flat, unshielded, front mounting

For IEL/IET/Trapeziform Type 2 handle

SPECIFICATIONS

Depth:	2.5mm
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel for Handle (PIU)

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
----------------	-------------	------------	------------------	-------------	----------	--------------

30848-327	3U	4HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-328	3U	5HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-329	3U	6HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-330	3U	7HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-336	6U	4HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-331	3U	8HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-333	3U	10HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-337	6U	5HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-338	6U	6HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-335	3U	12HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-339	6U	7HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-340	6U	8HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-342	6U	10HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized
30848-344	6U	12HP	1	IEL, IET, Trapezoid, Type 2	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Width
-------------------	-------------	---------------	---------------	---------------	--------	-------

30848-327	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	20mm
30848-328	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	25mm
30848-329	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	30.1mm
30848-330	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	35.2mm
30848-336	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	20mm
30848-331	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	40.3mm
30848-333	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	50.5mm
30848-337	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	25mm
30848-338	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	30.1mm
30848-335	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	128.4mm	60.6mm
30848-339	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	35.2mm
30848-340	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	40.3mm
30848-342	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	50.5mm
30848-344	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	No	261.8mm	60.6mm

Table 3/3

Catalog Number	Quick Ship
----------------	------------

30848-327	No
30848-328	No
30848-329	No
30848-330	No
30848-336	No
30848-331	No
30848-333	No
30848-337	No
30848-338	No
30848-335	No
30848-339	No
30848-340	No
30848-342	No
30848-344	No

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE