

Varistar CP Side Panel, Divided, With Quick-Release Fastener and Lock



Side panels (2 pieces) with Quick-Release Fastener without grounding kit for Varistar CP cabinets.

FEATURES

Steel, 1 mm

2 splitted Side panel without grounding kit

Safety lock kit included

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-061	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-062	42U	2000mm	1100mm	2	Black Grey	RAL 7021
21630-063	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-067	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-068	47U	2200mm	1100mm	2	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-069	47U	2200mm	1200mm	2	Black Grey	RAL 7021
21630-073	52U	2450mm	1000mm	2	Black Grey	RAL 7021
21630-074	52U	2450mm	1100mm	2	Black Grey	RAL 7021
21630-075	52U	2450mm	1200mm	2	Black Grey	RAL 7021

Table 2/2

Catalog Number	Finish	Material	Type	Quick Ship
21630-061	Powder Coated	Steel	Side Panel, Quick Release	No
21630-062	Powder Coated	Steel	Side Panel, Quick Release	No
21630-063	Powder Coated	Steel	Side Panel, Quick Release	No
21630-067	Powder Coated	Steel	Side Panel, Quick Release	No
21630-068	Powder Coated	Steel	Side Panel, Quick Release	No
21630-069	Powder Coated	Steel	Side Panel, Quick Release	No
21630-073	Powder Coated	Steel	Side Panel, Quick Release	No
21630-074	Powder Coated	Steel	Side Panel, Quick Release	No
21630-075	Powder Coated	Steel	Side Panel, Quick Release	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE