

# Stainless Steel Glazed Doors, DNGS



Electrical components can be viewed while the transparent stainless steel door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

## FEATURES

Description: Transparent door fitted with clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking programme.

Material: Frame: 2 mm AISI 304 stainless steel plate, AISI 316L (on request). Viewing area: 4 mm clear safety glass.

Finish: 400 pre-grained stainless steel.

Protection: IP 55, TYPE 12, 13, IK 07.

Mounting requirements: Use hinge kit DNMKS01 if not for replacement of standard door.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Brushed  
**Material:** Stainless Steel 304

Table 1/1

| Catalog Number | Height | Width  | Depth | Window Size  | Enclosure Material | Product Family |
|----------------|--------|--------|-------|--------------|--------------------|----------------|
| DNGS1610       | 1600mm | 1000mm | 17mm  | 1376 x 815mm | Mild Steel         | Free-Standing  |
| DNGS1810       | 1800mm | 1000mm | 17mm  | 1576 x 815mm | Mild Steel         | Free-Standing  |
| DNGS2010       | 2000mm | 1000mm | 17mm  | 1776 x 815mm | Mild Steel         | Free-Standing  |
| DNGS2006       | 2000mm | 600mm  | 17mm  | 1776 x 415mm | Mild Steel         | Free-Standing  |
| DNGS1606       | 1600mm | 600mm  | 17mm  | 1376 x 415mm | Mild Steel         | Free-Standing  |
| DNGS1608       | 1600mm | 800mm  | 17mm  | 1376 x 615mm | Mild Steel         | Free-Standing  |
| DNGS1408       | 1400mm | 800mm  | 17mm  | 1176 x 615mm | Mild Steel         | Free-Standing  |
| DNGS1806       | 1800mm | 600mm  | 17mm  | 1576 x 415mm | Mild Steel         | Free-Standing  |
| DNGS2008       | 2000mm | 800mm  | 17mm  | 1776 x 615mm | Mild Steel         | Free-Standing  |
| DNGS1808       | 1800mm | 800mm  | 17mm  | 1576 x 615mm | Mild Steel         | Free-Standing  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**