

# Varistar CP Steel Door, Plain With 3-Point Locking, IP20

## Power Utilities

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

### FEATURES

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Complies With               |
|----------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-104      | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-105      | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-106      | 52 U        | 2450 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-107      | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-108      | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-109      | 52 U        | 2450 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-432      | 24 U        | 1200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Complies With               |
|---------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-433     | 24 U        | 1200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-434     | 29 U        | 1400 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-435     | 29 U        | 1400 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-436     | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-437     | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-438     | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-439     | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

Table 2/2

| Catalog Number | Locking Type    | Product Type | Protection Rating | Type       | Works With  |
|----------------|-----------------|--------------|-------------------|------------|-------------|
| 21630-104      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-105      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-106      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-107      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-108      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-109      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-432      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-433      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-434      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-435      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |

| Catalog Number | Locking Type    | Product Type | Protection Rating | Type       | Works With  |
|----------------|-----------------|--------------|-------------------|------------|-------------|
| 21630-436      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-437      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-438      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |
| 21630-439      | 3-Point Locking | Cabinet Door | IP20              | Steel Door | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**