

# Monitor, Keyboard, Touchpad, 1 U Drawer



Designed for standard 19" rackmount designed for comfort  
robust design for heavy use or harsh environment operation

## CERTIFICATIONS



## FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

## SPECIFICATIONS

**Depth:** 470mm

**Product Type:** Cabinet/Rack Drawer

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Color     | Color Code | Type                        | Works With   |
|----------------|-------------|------------------|-----------|------------|-----------------------------|--------------|
| 60118-580      | 1U          | 1                | Jet Black | RAL 9005   | Monitor, Keyboard, Touchpad | 19" Cabinets |

| CatalogNumber | Rack Height | Package Quantity | Color     | Color Code | Type                              | Works With   |
|---------------|-------------|------------------|-----------|------------|-----------------------------------|--------------|
| 60118-582     | 1U          | 1                | Jet Black | RAL 9005   | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets |
| 60118-581     | 1U          | 1                | Jet Black | RAL 9005   | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets |

Table 2/2

| Catalog Number | Keyboard Type | Quick Ship |
|----------------|---------------|------------|
| 60118-580      | QWERTY UK     | No         |
| 60118-582      | AZERTY        | No         |
| 60118-581      | QWERTZ        | No         |

## ADDITIONAL PRODUCT DETAILS

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**