

EM-MR Conduit to Flange Clip with Retainer



FEATURES

Only one piece to install

Fast hammer-on installation

Pre-riveted retainer strap is easily bent into position

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

| Table 1/1 | | | |
|----------------|----------------|------------------|-------------|
| Catalog Number | Outer Diameter | Flange Thickness | Static Load |
| CM24812M | 18 - 30 mm | 3.2 - 6.4 mm | 330N |
| CM2416M | 23.4 - 35 mm | 3.2 - 6.4 mm | 330N |
| CM5816M | 23.4 - 35 mm | 7.9 - 12.7 mm | 330N |
| CM58812M | 18 - 30 mm | 7.9 - 12.7 mm | 330N |
| CM912812M | 18 - 30 mm | 14.3 - 19.1 mm | 330N |
| CM91216M | 23.4 - 35 mm | 14.3 - 19.1 mm | 330N |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

