

Branch Line Restraint Pipe Attachment

Data Solutions



CERTIFICATIONS



FEATURES

Accepts 3/8" or 1/2" (M10 or M12) threaded rod

Quick grip clamp simplifies measuring and cutting of threaded rod

Eliminates need to cut threaded rod to exact dimensions

Works with rough-cut threaded rod and eliminates pipe-side deburring

Can be installed with threaded rod above or below the service pipe

Shear-off head helps ensure correct torque and simplifies inspection

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	Height (H)	Length (L)
----------------	----------------	-------	---------------------	---------------	------------	------------

CSBBRP0200E G	404480	50	60.3mm	10, 12	100.3mm	68.3mm
CSBBRP0125E G	404478	32	42.2mm	10, 12	82.6mm	50mm
CSBBRP0100E G	404477	25	33.4mm	10, 12	73.7mm	41.4mm
CSBBRP0150E G	404479	40	48.3mm	10, 12	88.9mm	56.1mm

Table 2/2		
Catalog Number	Article Number	Width (W)
CSBBRP0200EG	404480	22.2mm
CSBBRP0125EG	404478	22.2mm
CSBBRP0100EG	404477	22.2mm
CSBBRP0150EG	404479	22.2mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE