

Cable to Web of Rail T20 Complete Welder Pair, Power, 85-141 lb T-Rail, 2/0 Concentric

Data Solutions

CATALOG NUMBER

PBWT202G



FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Each part number Includes both right and left hand welders

Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

Material: Graphite; Steel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 2/0 Concentric

Conductor Outer Diameter, Nominal: 10.62mm

Welder Style: T20

Mold Only: No

Replacement Mold: PBW2G

Welding Material: PB90, Sold Separately

Handle Clamp: C105B x 2, Sold Separately

Conductor Sleeve: S03F, Sold Separately

Hammer Die: WD84, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE