

Non-Insulated Stranded Conductor



FEATURES

Stranded pure electrolytic copper cable conductors for a variety of applications

Stranded grounded conductor cut into standard lengths for easy field installation

SPECIFICATIONS

Conductor Type: Concentric


Material: Copper

Table 1/2							
Catalog Number	Number of Wires	Wire Diameter	Diameter (Ø)	Length (L)	Cross Section	Conductor Size	
A800A09F65	19	2.13mm	10.6 mm	19.81m	67.4mm²	2/0 Stranded	
A800A22F100	19	2.69mm	13.4 mm	30.5m	107mm²	4/0 Stranded	

Table 2/2				
Catalog Number	Unit Weight			
A800A09F65	12.1 kg			
A800A22F100	30 kg			

Outer diameter dimensions are approximate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

TRACHTE

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF