

Flexibar Advanced Kit, 250 A, Three Phase

CATALOG NUMBER

FLXADVKIT250AT



FEATURES

Connects busbar to fixed switchgear

Kit includes preformed nVent ERIFLEX Flexibar Advanced with punched ends and end covers

Kit can be used in three configurations

Insulated by high-resistance, halogen free, flame retardant and low smoke material with less than 20% contact with conductor for high flexibility

Tinned copper allows for copper or aluminum conductor connections

RoHS compliant

PRODUCT ATTRIBUTES

Article Number: 534800

Typical Application Current Rating: 250 A

Flammability Rating: UL® 94V-0

Halogen Free Rating: UL® 2885;IEC® 60754-1;IEC® 62821-1

Low Smoke Rating: IEC® 61034-2;ISO 5659-2;UL® 2885

Smoke, Toxicity and Acidity Rating: IEC® 60754-2

UV Resistance Rating: UL® 854;UL® 2556

Type: Three Phase

Unit Weight: 0.76 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE