

Cable Entry Gland Plate Round Counter Nut, CCFRMNUT



FEATURES

CCFRMNUT Counter Nut only; CCFRBK Frame and CCFRM Locking Adapter sold separately

IP66 Modular Halogen-free and silicone free cable entry system, that provide versatility, variability and variety

The frames, inlays and grommets can be combined in many ways - ensuring you many versatile configuration options

No need to disassemble and reconnect connectors on cables so manufactures warranty is not voided

CCFR cable entry is quick and easy to assemble

It is made of a sturdy, glass-fiber reinforced plastic

CCFG grommets needs to be ordered separately

CCFD dividers are bought separately as needed

Operating Temperature: -40 to 120 °C / -40 to 248 °F

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
CCFRM20NUT	59678	28mm	30mm	7mm	Thermoplastic Elastomer	Smooth Matte
CCFRM25NUT	59679	28mm	30mm	7mm	Thermoplastic Elastomer	Smooth Matte
CCFRM32NUT	59681	28mm	30mm	7mm	Thermoplastic Elastomer	Smooth Matte
CCFRM40NUT	59682	49mm	53mm	7mm	Thermoplastic Elastomer	Smooth Matte
CCFRM50NUT	59683	49mm	53mm	7mm	Thermoplastic Elastomer	Smooth Matte
CCFRM63NUT	59684	49mm	53mm	7mm	Thermoplastic Elastomer	Smooth Matte

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE