

# ProLine G2 High-Performance Pagoda Exhaust Vent Cutout Top

The High-Performance Pagoda Exhaust Vent Cutout Top has a cutout that accepts one high-performance pagoda vent.



## FEATURES

Cutout top for High-Performance, Pagoda Exhaust Vents

Bolts are furnished to hold top in position (lifting eyes can be used in place of bolts)

Seamless, polyurethane gasket between top and frame (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Ground studs are included

Note: A High Performance Pagoda Exhaust Vent can be used with any ProLine G2 solid top by requesting a cutout modification

SPECIFICATIONS

**Thickness:** 1.52mm  
**Color:** Light Gray  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |                |            |            |
|----------------|----------------|------------|------------|
| Catalog Number | Article Number | Material   | Quick Ship |
| P2TPH88        | 32717          | Mild Steel | No         |
| P2TPH66        | 32714          | Mild Steel | No         |
| P2TPH86        | 32716          | Mild Steel | No         |
| P2TPH68        | 32715          | Mild Steel | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE