

Elbow 90-Degree Lay-in Painted

Power Utilities



Lay-in Painted 90-Degree Elbows have all removable sides, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.

FEATURES

Lay-in Painted 90-Degree Elbows have all removable sides, retaining lay-in feature regardless of how the elbow is oriented

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sides are held together with screws

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Finish: Powder Coated

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Material	Thickness
F1010G90E	45590	Elbow	254 mm	254 mm	Mild Steel	1.9 mm
F1212G90E	51890	Elbow	305 mm	305 mm	Mild Steel	1.9 mm
F22G90E	52510	Elbow	64 mm	64 mm	Mild Steel	1.52 mm

CatalogNumber	Article Number	Type	Height	Width	Material	Thickness
F33G90E	15486	Elbow	76 mm	76 mm	Mild Steel	1.52 mm
F44G90E	52520	Elbow	102 mm	102 mm	Mild Steel	1.52 mm
F66G90E	52530	Elbow	152 mm	152 mm	Mild Steel	1.52 mm
F88G90E	52780	Elbow	203 mm	203 mm	Mild Steel	1.9 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE