

Basic PDU, EB0xxx, 400 VAC, 3-PH

Modular, compact PDU. Ultra-Low Profile Design



FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EB0403	Enlogic	Basic PDU	Socket Strip	(36) C13, (6) C19	42	Black
EB0450	Enlogic	Basic PDU	Socket Strip	(21) C13/C19	42	Black
EB0811	Enlogic	Basic PDU	Socket Strip	(30) C13, (12) C19	42	Black
EB0850	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black

Table 2/6

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Length	Input Cable Location
EB0403	No Circuit Breaker	No	0	11.0 kVA	3m	Top Feed

CatalogNumber	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Length	Input Cable Location
EB0450	No Circuit Breaker	No	0	11.5 kVA North America, 11.0 kVA International	1.8m	Top Feed
EB0811	16 A, 1-pole, Hy-Mag	No	6	22.0 kVA	3m	Top Feed
EB0850	16 A, 1-pole, Hy-Mag	No	6	17.3 kVA North America, 22.1 kVA International	1.8m	Top Feed

Table 3/6

Catalog Number	Input Voltage	Phase	Nominal Voltage	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EB0403	380 – 415V	3 PH	415V	11.0 kVA	No	16 A
EB0450	380 – 415V	3 PH	415V	11.5 / 11.0 kVA	No	20 A (16 A) North America, 16 A International
EB0811	380 – 415V	3 PH	415V	22.0 kVA	No	32 A
EB0850	380 – 415V	3 PH	415V	17.3 / 22.1 kVA	No	30 A (24 A) North America, 32 A International

Table 4/6

Catalog Number	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
EB0403	230VAC	0U	IEC 60309 516P6 (IP44)	None	No	Steel
EB0450	208 – 230VAC	0U	IEC 60309 520P6/516P6	None	No	Steel
EB0811	230VAC	0U	IEC 60309 532P6 (IP44)	None	No	Steel
EB0850	208 – 230VAC	0U	IEC 60309 530P6/532P6	None	No	Steel

Table 5/6

Catalog Number	Finish	Height	Width	Depth	Weight	Package Quantity
EB0403	Powder Coated	1490mm	52mm	53mm	6.11kg	1
EB0450	Powder Coated	1490mm	56mm	55mm	9.5kg	1
EB0811	Powder Coated	1750mm	55mm	53mm	9.02kg	1
EB0850	Powder Coated	1780mm	56mm	55mm	10kg	1

Table 6/6

Catalog Number	Quick Ship
EB0403	No
EB0450	No
EB0811	No
EB0850	No

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE