

# Plug-In Unit Kit With IET Handle, Shielded, Black, 6 U



Plug-in unit, with IET inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

## CERTIFICATIONS



## FEATURES

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

## SPECIFICATIONS

|                       |                               |
|-----------------------|-------------------------------|
| <b>Rack Height:</b>   | 6U                            |
| <b>Material:</b>      | Aluminum                      |
| <b>Finish:</b>        | Anodized; Passivated          |
| <b>Product Type:</b>  | Front Panel                   |
| <b>Type:</b>          | Front Panel with Handle (PIU) |
| <b>EMC Shielding:</b> | Yes                           |

Table 1/2

| Catalog Number | Rack Width | Package Quantity | Handle Type | Mounting       | Gasket Type | Front Finish |
|----------------|------------|------------------|-------------|----------------|-------------|--------------|
| 20848-766      | 4HP        | 1                | IET         | Screw-on Front | Textile EMC | Anodized     |
| 20848-767      | 8HP        | 1                | IET         | Screw-on Front | Textile EMC | Anodized     |
| 20848-768      | 12HP       | 1                | IET         | Screw-on Front | Textile EMC | Anodized     |

Table 2/2

| Catalog Number | Rear Finish | Treated Edges | Complies With                                                  | Height  | Width  | Quick Ship |
|----------------|-------------|---------------|----------------------------------------------------------------|---------|--------|------------|
| 20848-766      | Etched      | No            | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 261.8mm | 20mm   | No         |
| 20848-767      | Etched      | No            | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 261.8mm | 40.3mm | No         |
| 20848-768      | Etched      | No            | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 261.8mm | 60.6mm | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**