

# nVent CADDY Speed Link SLS with Wedge Anchor



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and wedge anchor from Powers Fasteners, Inc.

Quickly and easily attaches into cracked and non-cracked concrete

Installs in strut profiles without the need to insert fingers or tools into the strut

Finger tightening of nut secures the locking device into position without tools

No special tools required

ETA-13/0355 assessment available for wedge anchor from Powers Fasteners, Inc

## SPECIFICATIONS

<b>Wire Rope Diameter:</b>	2 mm
<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel;Polypropylene;Zinc Alloy
<b>Complies With:</b>	SMACNA HVAC-DCS

Table 1/2

Catalog Number	Article Number	Wire Rope Length	Length (L)	Drill Bit Diameter	Drill Hole Depth	Embedment Depth
SLS2L3WA6	196759	3m	63.5mm	6mm	60mm	55 mm Min
SLS2L5WA6	196760	5m	63.5mm	6mm	60mm	55 mm Min

Table 2/2

Catalog Number	Article Number	Static Load
SLS2L3WA6	196759	270N
SLS2L5WA6	196760	270N

**Slot Size (SS):** 8 x 6.5 mm - 8 x 10 mm

**Hole Size (HS):** 8 - 10 mm

**Width (W):** 16 mm

**Height 2 (H2):** 43.5mm

**Height 1 (H1):** 53mm

**Thread Size (TS):** M8


**Thickness (T):** 4 mm Max

## ADDITIONAL PRODUCT DETAILS

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

