

Crimping Compression Tool, Manual

Data Solutions

CATALOG NUMBER

M2M



FEATURES

Wide cross section range

Ergonomic design

Lightweight and easy to use

Includes easy-to-carry custom case

PRODUCT ATTRIBUTES

Article Number: 716900

System: Manual

Dies: RKM2 series; PKM2 series

Crimping Shape: Hexagon

Conductor Size: #10 Stranded - 600 kcmil Stranded; 6 mm² Stranded - 300 mm² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE