

Air Terminal Base, Imperial Thread



CERTIFICATIONS



FEATURES

Install with adhesive or screw down fixings

Mechanical connection recommended for vertical installation

Positive single bolt tension for multi-directional cable clamping

SPECIFICATIONS

Finish:	Bare
Conductor Size, UL:	Class 1 - Class 2 (4/0 Max)
Material:	Copper


Table 1/2

Catalog Number	Thread Size (TS)	Mounting	Hole Size (HS)	Depth (D)	Height (H)	Width (W)
LPC30512	1/2" UNC	Horizontal or Vertical	6.35 mm	73.7mm	25.4 mm	77.9 mm
LPC30558V	5/8" UNC	Vertical	6.35 mm	73.7mm	25.4 mm	77.9 mm

CatalogNumber	Thread Size (TS)	Mounting	Hole Size (HS)	Depth (D)	Height (H)	Width (W)
LPC30558H	5/8" UNC	Horizontal	6.35 mm	73.7mm	25.4 mm	77.9 mm

Table 2/2	
Catalog Number	Unit Weight
LPC30512	0.38 kg
LPC30558V	0.38 kg
LPC30558H	0.38 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE