

Joint Bond Mold Pair Only, Power



FEATURES

Pair of replacement molds with mounting parts designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Bond Terminal Style: C

Material: Graphite

Table 1/1

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal
PBCX3M	UIC	50 mm ² Ropelay	9.13mm
PBCX6M	UIC	120 mm ² Ropelay	9.53mm
PBC2JM	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm
PBCS5M	85 lb to 141 lb T-Rail Sections	2/0 Composite	13.36mm
PBCS6M	85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal
PBC2SM	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm
PBCY5X5M	UIC	95 mm ² Ropelay	15.52mm
PBC2WM	85 lb to 141 lb T-Rail Sections	250 kcmil Stranded	19.05mm
PBXLC2WM	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE