

Varistar CP Seismic Cabinet, Bellcore Zone 4, EMC

Power Utilities

FEATURES

Earthquake secure up to Bellcore Zone 4, tested with 250 KGs per Telcordia GR-63 Core

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

SPECIFICATIONS

Table 1/3

| Catalog Number | Frame Material | Rack Height | Height | Width | Depth | Static Load |
|----------------|----------------|-------------|---------|--------|--------|-------------|
| 10630-050 | Steel | 42 U | 2000 mm | 600 mm | 800 mm | 1600 kgf |

Table 2/3

| Catalog Number | Protection Rating | Complies With | Color | Color Code | Material | Shock and Vibration Tolerance |
|----------------|-------------------|--|------------|------------|----------|-------------------------------|
| 10630-050 | IP55 | IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3, IEC 61587-1, IEC 61587-2, EN 45545-2 | Black Grey | RAL 7021 | Steel | 5 g (force) |

Table 3/3

| Catalog Number | Works With |
|----------------|------------|
|----------------|------------|

| | |
|-----------|-------------|
| 10630-050 | Varistar CP |
|-----------|-------------|

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE