

# 19" Fan Unit, 1 U, Speed Control and Monitoring

Fan Unit for installation into a 1 U space within the Cabinet.



## CERTIFICATIONS



## FEATURES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

## SPECIFICATIONS

Table 1/2

| Catalog Number | Input Voltage AC | Input Voltage DC | Package Quantity | Finish                         | Material        | Certifications |
|----------------|------------------|------------------|------------------|--------------------------------|-----------------|----------------|
| 10713-098      |                  | 24V min          | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | CE, EAC, RoHS  |
| 19713-006      | 230V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | CE, EAC, RoHS  |

| CatalogNumber | Input Voltage AC | Input Voltage DC | Package Quantity | Finish                         | Material        | Certifications |
|---------------|------------------|------------------|------------------|--------------------------------|-----------------|----------------|
| 10713-099     |                  | 24V min          | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | RoHS, CE, EAC  |
| 19713-121     | 230V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | RoHS, EAC      |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 10713-098      | No         |
| 19713-006      | No         |
| 10713-099      | No         |
| 19713-121      | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**