

# Interscale for Embedded NUC, Conduction Cooled, 44 x 112 x 107 mm

### **CATALOG NUMBER**

# 14830-002





Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

# **CERTIFICATIONS**



### **FEATURES**

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Compliant with the SDT.03 embeddedNUC standard http://www.sget.org/standards.html

Cutouts specific for IES MB95 embedded NUC board (http://en.ies.de/)

Integrated EMC protection

Integrated heat sink on top cover with 5 mm heat fins

Rigid construction requires only two screws

Color RAL 7016

Board mounting studs installed

Other dimensions, cutout shapes or locations, and screen printing available

### **PRODUCT ATTRIBUTES**

Product Type: Small Form Factor Case

Product Family: Interscale

Type: Desktop

Height: 43.7mm

Width: 112mm

Depth: 106.5mm

Material: Aluminum

Color: Anthracite Grey

Color Code: RAL 7016

Finish: Powder Coated

Protection Rating: IP20

Cooling: Conduction Cooled

Package Quantity: 1

Net Weight: 0.3kg

# ADDITIONAL PRODUCT DETAILS

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

# **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

# Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE