

Front Panel, Unshielded, With Fastener Pin



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICATIONS



FEATURES

Enable grounding of the front area (protection class 1)

SPECIFICATIONS

Depth:	2.5mm
Rack Height:	3U
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle

Table 1/2

Catalog Number	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-159	7HP	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-163	42HP	1	Screw-on Front	Anodized	Conductive	No
20119-162	28HP	1	Screw-on Front	Anodized	Conductive	No
20119-161	21HP	1	Screw-on Front	Anodized	Conductive	No
20119-160	14HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Catalog Number	Complies With	EMC Shielding	Height	Width	Quick Ship
20119-159	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	35.2mm	No
20119-163	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm	No
20119-162	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm	No
20119-161	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	106.3mm	No
20119-160	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	70.8mm	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE