


# Novastar Frame, Universal Heavy-Duty



Asthetic aluminum extruded frame with 400 kg static load capacity. 19" upright built into the frame.

## CERTIFICATIONS

---



## FEATURES

---

Novastar Frame, Universal Heavy-Duty

Aluminium profile, RAL 7021, including grounding

Static load-carrying capacity 400 kg

## SPECIFICATIONS

---

|                        |                    |
|------------------------|--------------------|
| <b>Static Load:</b>    | 400kg              |
| <b>Frame Material:</b> | Aluminum           |
| <b>Material:</b>       | Aluminum           |
| <b>Product Type:</b>   | Cabinet/Rack Frame |

Table 1/2

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 28230-052      | 47U         | 2145mm | 553mm | 900mm  | 1                | Black Grey |
| 28230-053      | 47U         | 2145mm | 553mm | 1000mm | 1                | Black Grey |
| 28230-057      | 12U         | 589mm  | 553mm | 500mm  | 1                | Black Grey |
| 28230-058      | 12U         | 589mm  | 553mm | 600mm  | 1                | Black Grey |
| 28230-059      | 12U         | 589mm  | 553mm | 800mm  | 1                | Black Grey |
| 28230-107      | 12U         | 589mm  | 553mm | 900mm  | 1                | Black Grey |
| 28230-108      | 12U         | 589mm  | 553mm | 1000mm | 1                | Black Grey |
| 28230-109      | 16U         | 767mm  | 553mm | 500mm  | 1                | Black Grey |
| 28230-110      | 16U         | 767mm  | 553mm | 600mm  | 1                | Black Grey |
| 28230-111      | 16U         | 767mm  | 553mm | 800mm  | 1                | Black Grey |
| 28230-112      | 16U         | 767mm  | 553mm | 900mm  | 1                | Black Grey |
| 28230-113      | 16U         | 767mm  | 553mm | 1000mm | 1                | Black Grey |
| 28230-114      | 20U         | 945mm  | 553mm | 500mm  | 1                | Black Grey |
| 28230-115      | 20U         | 945mm  | 553mm | 600mm  | 1                | Black Grey |
| 28230-116      | 20U         | 945mm  | 553mm | 800mm  | 1                | Black Grey |
| 28230-117      | 20U         | 945mm  | 553mm | 900mm  | 1                | Black Grey |
| 28230-118      | 20U         | 945mm  | 553mm | 1000mm | 1                | Black Grey |
| 28230-119      | 25U         | 1167mm | 553mm | 500mm  | 1                | Black Grey |

| <b>CatalogNumber</b> | <b>Rack Height</b> | <b>Height</b> | <b>Width</b> | <b>Depth</b> | <b>Package Quantity</b> | <b>Color</b> |
|----------------------|--------------------|---------------|--------------|--------------|-------------------------|--------------|
| 28230-167            | 25U                | 1167mm        | 553mm        | 600mm        | 1                       | Black Grey   |
| 28230-168            | 25U                | 1167mm        | 553mm        | 800mm        | 1                       | Black Grey   |
| 28230-169            | 25U                | 1167mm        | 553mm        | 900mm        | 1                       | Black Grey   |
| 28230-170            | 25U                | 1167mm        | 553mm        | 1000mm       | 1                       | Black Grey   |
| 28230-171            | 34U                | 1567mm        | 553mm        | 500mm        | 1                       | Black Grey   |
| 28230-172            | 34U                | 1567mm        | 553mm        | 600mm        | 1                       | Black Grey   |
| 28230-173            | 34U                | 1567mm        | 553mm        | 800mm        | 1                       | Black Grey   |
| 28230-174            | 34U                | 1567mm        | 553mm        | 900mm        | 1                       | Black Grey   |
| 28230-175            | 34U                | 1567mm        | 553mm        | 1000mm       | 1                       | Black Grey   |
| 28230-176            | 38U                | 1745mm        | 553mm        | 500mm        | 1                       | Black Grey   |
| 28230-177            | 38U                | 1745mm        | 553mm        | 600mm        | 1                       | Black Grey   |
| 28230-178            | 38U                | 1745mm        | 553mm        | 800mm        | 1                       | Black Grey   |
| 28230-179            | 38U                | 1745mm        | 553mm        | 900mm        | 1                       | Black Grey   |
| 28230-180            | 38U                | 1745mm        | 553mm        | 1000mm       | 1                       | Black Grey   |
| 28230-181            | 43U                | 1967mm        | 553mm        | 500mm        | 1                       | Black Grey   |
| 28230-182            | 43U                | 1967mm        | 553mm        | 600mm        | 1                       | Black Grey   |
| 28230-183            | 43U                | 1967mm        | 553mm        | 800mm        | 1                       | Black Grey   |
| 28230-184            | 43U                | 1967mm        | 553mm        | 900mm        | 1                       | Black Grey   |

| CatalogNumber | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 28230-185     | 43U         | 1967mm | 553mm | 1000mm | 1                | Black Grey |
| 28230-186     | 47U         | 2145mm | 553mm | 500mm  | 1                | Black Grey |
| 28230-187     | 47U         | 2145mm | 553mm | 600mm  | 1                | Black Grey |
| 28230-188     | 47U         | 2145mm | 553mm | 800mm  | 1                | Black Grey |
| 28230-221     | 29U         | 1345mm | 553mm | 500mm  | 1                | Black Grey |
| 28230-222     | 29U         | 1345mm | 553mm | 600mm  | 1                | Black Grey |
| 28230-223     | 29U         | 1345mm | 553mm | 800mm  | 1                | Black Grey |
| 28230-224     | 29U         | 1345mm | 553mm | 900mm  | 1                | Black Grey |
| 28230-225     | 29U         | 1345mm | 553mm | 1000mm | 1                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Finish        | Type      | Certifications | Quick Ship |
|----------------|------------|---------------|-----------|----------------|------------|
| 28230-052      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-053      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-057      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-058      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-059      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-107      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-108      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-109      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |

| Catalog Number | Color Code | Finish        | Type      | Certifications | Quick Ship |
|----------------|------------|---------------|-----------|----------------|------------|
| 28230-110      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-111      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-112      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-113      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-114      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-115      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-116      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-117      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-118      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-119      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-167      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-168      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-169      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-170      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-171      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-172      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-173      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-174      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |

| Catalog Number | Color Code | Finish        | Type      | Certifications | Quick Ship |
|----------------|------------|---------------|-----------|----------------|------------|
| 28230-175      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-176      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-177      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-178      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-179      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-180      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-181      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-182      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-183      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-184      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-185      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-186      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-187      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-188      | RAL 7021   | Powder Coated | Universal | RoHS           | No         |
| 28230-221      | RAL 7021   | Powder Coated | Universal |                | No         |
| 28230-222      | RAL 7021   | Powder Coated | Universal |                | No         |
| 28230-223      | RAL 7021   | Powder Coated | Universal |                | No         |
| 28230-224      | RAL 7021   | Powder Coated | Universal |                | No         |

| Catalog Number | Color Code | Finish        | Type      | Certifications | Quick Ship |
|----------------|------------|---------------|-----------|----------------|------------|
| 28230-225      | RAL 7021   | Powder Coated | Universal |                | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**